# **Sterile Pass Box:**



Model	AL-PB500	AL-PB600	AL-PB800	
External Size (mm)	W660×D500×H590	W760×D600×H690	W1640×D740×H2050	
Internal Size (mm)	W500×D500×H500	W600×D600×H600	W1550×D645×H800	
Material	Outer Cabin: epoxy powder coated steel or stainless steel Inner Cabin: stainless steel			
Material Thickness	1.0/1.2/1.5			
Interlock	Mechanical Interlock / Electronic Interlock			
Glass View	380*380*8	480*480*8	480*480*8	
	Tempered Glass/Vacuum Glass			
Sterilization Lamp	18W			
Power Supply	220V/50Hz	220V/50Hz	220V/50Hz	

## **AIR SHOWER PASS BOX:**



Model		AL-APB500	AL-APB600	AL-APB800	
External Size (mm)		W740×D500×H1300	W840×D600×H1400	W1040×D800×H1600	
Internal Size (mm) W500×D500×H500 W600×D600×H600 W800		W800×D800×H800			
Material		Outer Cabin: epoxy powder coated steel or stainless steel Inner Cabin: stainless steel			
Interlock		Electronic Interlock			
Air Velocity		>/=20m/s	>/=20m/s	>/=20m/s	
Nozzles	Material	SUS304 direction adjust(embedded type)			
	Quantity	4PCS	4PCS	6PCS	
Prefilter	Size(mm)	525*275*17	560*275*17	560*275*17	
	Efficiency	G4	G4	G4	
HEPA filter	Size(mm)	484*484*69	630*630*69	630*630*69	
	Efficiency	99.99%@0.3um	99.99%@0.3um	99.99%@0.3um	
Sterilization Lamp		18W×1	18W×1	18W×2	
Power		750W	750W	750W	
Power Supp	ly	220V/50Hz 220V/50Hz 220V/50Hz		220V/50Hz	

## **DYNAMIC PASS BOX:**



I	Model	AL-LPB500	AL-LPB600	AL-LPB800
External Size (mm)		W700×D500×H1000	W800×D600×H1100	W1000×D800×H1300
Internal Size (mm)		W500×D500×H500	W600×D600×H600	W800×D800×H800
Material		Full stainless steel 304/316		6
Interlock		Electronic Interlock		
Air Velocity		0.4-0.7m/s	0.4-0.7m/s	0.4-0.7m/s
		Perforated laminar flow plate		
Prefilter	Size(mm)	525*275*17	560*275*17	560*275*17
	Efficiency	G4	G4	G4
HEPA filter	Size(mm)	484*484*69	630*630*69	630*630*69
	Efficiency	99.99%@0.3um	99.99%@0.3um	99.99%@0.3um
Differential F	Pressure Gauge	American Dywer Brand		•
Clean Level		ISO5(209E standard)		
Sterilization Lamp		18W×1	18W×1	18W×2
Power		750W	750W	750W
Power Supp	ly	220V/50Hz	220V/50Hz 220V/50Hz	

#### PASS BOX PROJECT REFER1:

#### **PASS BOX PROJECT REFER2:**





#### **PASS BOX PROJECT REFER3:**



## PASS BOX PROJECT REFER4:



